NURSE CALL PAGING SYSTEM

Highlights:

- Compact & Light Nurse Call
- Improve productivity & service standard
- Nurse can perform multi-task
- Empower nurse to oversee a larger area
- Products are certified by **SIRIM**

HOSPITALITY SOLUTION

Email: info@QChannels.com

QCHANNELS Nurse Call Paging System was designed to help patients to contact the nurse or service staff direct from their bed or inside toilet.

Patients can now push a button on the unit to contact nurse. A message will be transmitted to the watch or display monitor, informing him the specific bed number that need help.



Nurse Call Watch Receiver (LM-D800L)



Nurse Call Single Button Waterproof Transmitter (LM-T9000F)



Nurse Call Display Receiver (LM-D303KF)









NURSE CALL PAGING SYSTEM

HOSPITALITY SOLUTION

Operation & Installation:

QCHANNELS Nurse Call Paging System consists of **Call** button to be placed beside bed. **Watch** to be held by nurse and a **Display** to be placed on the wall for nurse viewing.

Patient presses the button on the bed to contact the Nurse. **Display** will have sound alert and the table number will be displayed. At the same time, Nurse's **Watch** will vibrate and show the bed number and type of service requested.

Advantages:

- Compact & Light Table Call (Water Resistance or WaterProof models are available)
- Improve productivity and service standard
- Nurse or service staff can perform other duties and are readily alerted when patient requires assistance
- Empower service staff to oversee a larger area

Application

■ Hospital, Clinic, Nursing Home, and Specialist Centre

Email: info@QChannels.com



Specifications:

Table Call Transmitter (LM-T9000F/LM-HS1000F)

- ◀ Frequency: 433.92MHz
- ▼ FM Modulation
- ◆ Dimension:

 LM-T9000F: W60 X D60 X H16

 LM-HS1000F: 1.5m
- Single Button

- Replaceable Battery
- ◆ FCC Compliant: This device complies with FCC Rules, tested to comply with FCC Standards



Nurse Call Single Button WaterProof Transmitter (LM-T9000F)



Nurse Call Coil-Type Switch (LM-HS1000F)



Nurse Call Display Receiver (LM-D303KF)

Table Call Display Receiver (LM-D303KF)

- ◆ Frequency: 433.92MHz
- ▼ FM Modulation
- Display: 3 calls and more
- ◆ Dimension: W290 X D119 X H32
- 15 Melody Selectable

◀ KCC Certification: This device complies with KCC Rules, tested to comply with KCC Standards

Table Call Watch Receiver (LM-D800L)

- ◆ Frequency: 433.92MHz
- ▼ FM Modulation
- ◆ Display: 8 calls
- Dimension: W50 X D40 X H18
- ◀ Alert Mode: Vibration
- ◀ KCC Certification: This device complies with KCC Rules, tested to comply with KCC Standards



Nurse Call Watch Receiver (LM-D800L)



Q CHANNELS SDN. BHD. (1112243-M)

F-13A-05, PACIFIC PLACE SÌGNATURE ÓFFICE, JALAN PJU 1A/4A, 47301 PETALING JAYA, SELANGOR, MALAYSIA.

HOTLINE: 1700-81-9579 WEBSITE: www.QChannels.com